

EasyReach™ Cleaning Tool



Lightweight stainless steel flat mop tool

Contec's lightweight stainless steel EasyReach™ Cleaning Tool is designed for cleaning isolators, LAF hoods, glove boxes and other mini environments. It's rectangular shape overlapping straight-line action easy to achieve. Hinged joint along with the ability to lay flat makes this lightweight tool comfortable and easy to use for accessing hard-to-reach areas.






The single-use, multilayer cleaning pads are very absorbent, ensuring good even coverage of disinfectant or IPA. The easy grab edge on the cleaning pad ensures the pad fits tightly on the mop frame but is easy to be replaced with gloved hands. Dry pads are available ultrasonically sealed to provide a low level of particulates for use in product contact areas. Sterile knitted pads presaturated with 70% IPA are also available.

Features	Benefits
Versatile and easy to use	<ul style="list-style-type: none"> • Specially designed cleaning pad tab/grip enables quick and easy fitting to the frame with gloved hands • All tool options are designed to be easily passed through transfer hatches • Versatile low profile, layflat pivoting head ensures even the most awkward areas can be quickly reached with ease • Presaturated cleaning pad option removes the need for 70% IPA spray, minimizing transfer of materials and simplifying the cleaning procedure
Safe for users and equipment	<ul style="list-style-type: none"> • Reduces the risk of operators leaning into LAF hoods, opening isolators, intervening into RABS, and introducing contamination while attempting to ensure effective cleaning • Knitted presaturated pad option reduces operator exposure to high levels of VOCs typically experienced when using IPA spray bottles and reduces the volume of hazardous chemical storage • Rounded tool edges and strong, durable, double layer pads ensure equipment is not damaged during use • All components are designed to be chemical resistant, minimizing the risk of contamination from degradation
Ultrasonically sealed edges	<ul style="list-style-type: none"> • Dry pads are ultrasonically sealed and presaturated pads are sewn to generate less particles and fibers while remaining strong, durable, and compatible with common cleanroom solutions • The polyester cleaning pads leave no unwanted surface residues • Well-fitted quilted pad ensures effective, even surface coverage reducing the number of viable and nonviable contaminants and ensuring maximum residue removal

Part No.	Description	Size	Packaging
MEQT0021	EasyReach Cleaning Pads Ultrasonically sealed polyester	7.5" x 2.8" (190 x 71 mm)	4/bag; 25 bags/case
MEQT0022	EasyReach Sterile Cleaning Pads Ultrasonically sealed polyester	 7.5" x 2.8" (190 x 71 mm)	4/bag; 25 bags/case
PSME0001	EasyReach Sterile 100% knitted polyester cleaning pads, presaturated with 70% IPA/30% DI water	 7.5" x 2.8" (190 x 71 mm)	8/bag; 8 bags/case
2665LF	EasyReach layflat mop frame Stainless steel	16.5" (42 cm)	1/case
2685LF	QuickConnect EasyReach Layflat frame, stainless steel	7.5" (19 cm)	1/case
2685P	QuickConnect EasyReach Layflat frame, polypropylene	7.5" (19 cm)	1/case

Product Information

Cover material Cleaning pads 2685LF, 2665LF 2685P	<ul style="list-style-type: none"> • 100% knitted polyester • Type 304 stainless steel • Polypropylene (PP) 
Cover construction MEQT0021, MEQT0022 PSME0001	<ul style="list-style-type: none"> • Multilayer ultrasonically quilted; ultrasonically sealed • Multilayer ultrasonically quilted; sewn
Packaging materials	<ul style="list-style-type: none"> • Outer bags (OB1, OB2), low density polyethylene (LDPE)  • Case (CS), corrugated fiberboard (PAP) 
Environment	<ul style="list-style-type: none"> • ISO 4-8 Grade A/B for sterile, C/D for nonsterile
Shelf life	<ul style="list-style-type: none"> • Sterile: 2 years from manufacturing date



MEQT0021/MEQT0022

Recycle Symbols



Technical Data

	MEQT0021	MEQT0022	PSME0001	
Attribute (units)	Typical Value	Typical Value	Typical Value	Test Method
Mop weight, dry; (g)	18.68	18.68	240	CTM004-03
Sorbent capacity; (mL/mop)	73	73	63	CTM004-03
Particles, $P \geq 0.5\mu\text{m}$; ($\times 10^6/\text{m}^2$)	0.24	0.24	3.25	IEST-RP-CC004.2, Sec. 5.1
Fibers $\geq 100\mu\text{m}$; ($\times 10^3/\text{m}^2$)	0.01	0.01	0.22	IEST-RP-CC004.2, Sec. 5.2
Mop frames	2685LF, 2665LF, 2685P		2665LF, 2685P	

Packaging	EA/OB1	OB1/OB2	OB2/CS	EA/CS
MEQT0021	4	1	25	100
MEQT0022	4	1	25	100
PSME0001	8	4	2	64

EA = each; OB = outer bag 1/2; CS = case

Notes

- The data shown are typical values and should not be used as product specifications.
- Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Test Methods

- CTM = Refers to Contec Test Method.
- Mop coverage data is based on mop head applying solution such that the mopped surface is visibly wetted across the full mop path with no dry streaking observed, under controlled conditions. It is the responsibility of the user to determine appropriate coverage to ensure surfaces are visibly wet for the contact time required for their specific solution.